



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## KC15 9STR Post Split Bolt

*Burndy LLC*

Catalog Number	KC15
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Flat, 12 - 9 Awg (STR) / 12 - 8 Awg (Sol).
Weight per unit	0.0350 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Bronze, Leaded, Commercial
pallet quantity	44550

### Descriptions

Description	9STR POST SPLIT BOLT
extra long description	BUR KC15 12-9 STR 3/8 POST 1 COND
Long Description	Mechanical Grounding Connector, Cable to Flat, 12 - 9 AWG (Str) / 12 - 8 AWG (Sol).
Product Type	Mechanical
Special Features	Features: SERVIT POST Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar, One-Wrench Installation, Conductor Type: Run: Commercial Stranded Copper, Commercial Solid Copper, Cross Flats: 1/2, 3/8 IN, Height: 1-1/8 IN, Stud Size: 1/4-20, Dimension B: 3/8 IN

### Manufacturer Information

Brand	BURNDY
GTIN	00781810254004
Manufacturers Part Number	KC15
UPC	781810254004

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KC and K2C Series

### Packaging

Carton	1
Weight Per each	0.035

### Uses, Certifications, and Standards

Application	For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial
standard	UL467