



Type KC22B2

1/2-13  
stud size

**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

KC22J12T13  
7818101278722  
SERVIT POST MALE  
Active

**Web Use**  
BURNDY Product Line

**Dimensional**

Thread Size	1/2-13
Length (in)	1.50
Height (in)	1.00
Size (Hex) or Size (Bolt)	1/2
B Length (in)	0.41

**General**

**Product Description**  
Copper transformer ground connector. Fits all standard EEI-NEMA distribution transformers as tank grounding terminal, Cable Range: 8 Sol. - 2 Sol.

**Conductor(s)**

Copper Solid Size (Range)	8 AWG-2 AWG
Copper Stranded (Range)	N/A

**Physical**

Installation Torque	80
Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Leaded Bronze Alloy

**Approvals / Certifications**

Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175