




KCKF23, Mechanical Bulkhead Ground Connector Kit

By Burndy
Catalog # [KCKF23](#)



Mechanical Bulkhead Ground Connector Kit; Accommodates:
#8 - #2 AWG Stranded, #10 - #1 AWG Solid Copper; Nut
Torque: 275 in-lbs

Application

Designed to allow a ground wire to be connected from the inside of a box or enclosure to the outside of a box or enclosure

General

EU RoHS Indicator	Under Review
Material	Copper
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	100 LBS/in
Sub Brand	SERVIT POST
Trade Name	SERVIT POST™
Type	Bulkhead Servit
UPC	781810567432
UPC 12 Digit	7818105674322

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Size Range	10 AWG-1 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	4640

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50009515](#)



A proud member of the Hubbell Family.