

Eaton KRP-C-1200SP

Catalog Number: KRP-C-1200SP

Eaton Bussmann series KRP-C fuse, Current-limiting time-delay fuse, 1200 A, L, Non-indicating, Bolted blade end x bolted blade end, 4 sec at 500%, 300 kAIC at 600 V|100 kAIC Vdc, 600 V, 300 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series KRP-C fuse	KRP-C-1200SP
UPC	Product Length/Depth
051712605120	10.75 in
Product Height	Product Width
2.78 in	2.78 in
Product Weight	Warranty
4.15 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

Electrical rating

Amperage Rating

1200 A

Interrupt rating

300 kAIC at 600 Vac

100 kAIC Vdc

Response time

4 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Packaging type

Standard

General information

Class

Class L

Connection

Bolted blade end x bolted blade end

Fuse indicator

Non-indicating

Resources

Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - KRP-C-1200SP

Technical data sheets

KRP-C-1200SP~LOW-PEAK TIME-DELAY 300K

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton KRP-C-1200SP

Catalog Number: KRP-C-1200SP

Eaton Bussmann series KRP-C fuse, Current-limiting time-delay fuse, 1200 A, L, Non-indicating, Bolted blade end x bolted blade end, 4 sec at 500%, 300 kAIC at 600 V|100 kAIC Vdc, 600 V, 300 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series KRP-C fuse	KRP-C-1200SP
UPC	Product Length/Depth
051712605120	10.75 in
Product Height	Product Width
2.78 in	2.78 in
Product Weight	Warranty
4.15 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

Electrical rating

Amperage Rating

1200 A

Interrupt rating

300 kAIC at 600 Vac

100 kAIC Vdc

Response time

4 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Packaging type

Standard

General information

Class

Class L

Connection

Bolted blade end x bolted blade end

Fuse indicator

Non-indicating

Resources

Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - KRP-C-1200SP

Technical data sheets

KRP-C-1200SP~LOW-PEAK TIME-DELAY 300K

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia