




# KS17, Split Bolt Connector, Run/Tap: #8 AWG Str-#6 AWG Sol

By Burndy  
Catalog # [KS17](#)

Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap),Length:1.14.



## Application

For Direct Burial Applications In Earth Or Concrete, Copper

## General

Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	165
Material	Copper
Operating Temperature Celcius Max	90 °C
Operating Temperature Celcius Min	0 °C
Operating Temperature Range Celcius	0 - 90
Operating Temperature Range Fahrenheit	32 - 194
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810011508
UPC 12 Digit	7818100115088

## Dimensions

Dimension - B Length fraction	29/50 in
Dimension - B Length inch	.58 in
Dimension - Cross Flats inch	0.63 in
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.14
Dimension - Width fraction	9/20 in
Dimension - Width inch	0.45 in
Dimension - Width mm	11 mm
Width	0.45 in

## Conductor Related

Conductor - Copper Solid Run	6 AWG
Conductor - Copper Solid Run Range	8 AWG-6 AWG
Conductor - Copper Solid Tap	6 AWG
Conductor - Copper Solid Tap Range	14 AWG-6 AWG
Conductor - Copper Str Run	8 AWG;7 AWG;6 AWG
Conductor - Copper Str Run Range	8 STR - 6 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Tap Range	8 STR - 6 STR
Conductor - CopperWeld Solid Run	6 AWG
Conductor - CopperWeld Solid Run Range	6 AWG
Conductor - CopperWeld Solid Tap	6 AWG
Conductor - CopperWeld Solid Tap Range	6 AWG
Conductor - CopperWeld Str Run	9-1/2D ;8A ;3#12
Conductor - CopperWeld Str Run Range	9-1/2D -3#12
Conductor - CopperWeld Str Size	9-1/2 D;8A ;3#12
Conductor - CopperWeld Str Size Range	9-1/2 D-3#12
Conductor - CopperWeld Str Tap	9-1/2 D;8A ;3#12
Conductor - CopperWeld Str Tap Range	9-1/2 D-3#12
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul>

## Certifications and Compliance

Certification - CSA Approved No

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	99000

### Product Assets

- [3D Models - KS17\\_MODEL-STEP](#)
- [3D Models - KS17\\_MODEL-PDF](#)
- [3D Models - KS17\\_MODEL-IGES](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD..078561-01](#)



A proud member of the Hubbell Family.