

Eaton KTK-10

Catalog Number: KTK-10

Eaton Bussmann series KTK fuse, Control circuits, Lighting circuit protection, Meter circuits, 10 A, Non-indicating, Ferrule end x ferrule end, 100 kAIC at 600 V, Nickel-plated bronze endcap|Melamine tube, 600 V



General specifications

Product Name	Catalog Number
Eaton Bussmann series KTK fuse	KTK-10
UPC	EAN
051712420181	5027590063487
Product Length/Depth	Product Height
0.41 in	1.5 in
Product Width	Product Weight
0.41 in	0.19 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant

Electrical rating

Amperage Rating

10 A

Interrupt rating

100 kAIC at 600 Vac

Voltage rating

600 V

Physical details

Material

Melamine tube

Nickel-plated bronze endcap

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - KTK-10](#)

Technical data sheets

[KTK-10-LIMITRON FAST ACTING FUSE](#)

Technical service bulletins

[Datasheet - FNQ-30](#)