



## 20 AMP NEMA L1020 SINGLE RECEPTACLE

L1020R | [Pass & Seymour](#)

### FEATURES & BENEFITS

Turnlok Receptacle 3wire 20amp 125/250v



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### SPECIFICATIONS

#### GENERAL INFO

Type: Single Receptacles  
Number Of Wires: 3

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: Yes  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403  
UR: No

## DIMENSIONS

Depth (US): 1.19"

Height (US): 3.28"

Width (US): 1.61"

## TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L1020

Volts: 125/250V

Volts (AC): 125/250

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





## 20 AMP NEMA L1020 SINGLE RECEPTACLE

L1020R | [Pass & Seymour](#)

### FEATURES & BENEFITS

Turnlok Receptacle 3wire 20amp 125/250v



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### SPECIFICATIONS

#### GENERAL INFO

Type: Single Receptacles  
Number Of Wires: 3

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: Yes  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403  
UR: No

## DIMENSIONS

Depth (US): 1.19"

Height (US): 3.28"

Width (US): 1.61"

## TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L1020

Volts: 125/250V

Volts (AC): 125/250

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

