
30 AMP NEMA L1030 SINGLE RECEPTACLE

L1030R | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Single Receptacle 3wire 30amp 125/250v



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

SPECIFICATIONS

GENERAL INFO

Type: Single Receptacles
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No
CUL Listing No: No
cURus: No
Federal Spec: Yes
UL Listing No: 498
UL Standard: Yes
UN SPSC: 39121403
UR: No

DIMENSIONS

Depth (US): 1.28"
Height (US): 3.28"
Width (US): 1.61"

TECHNICAL INFORMATION

Amps: 30A
NEMA Configuration Number: L1030
Volts: 125/250V
Volts (AC): 125/250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

