



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L12HIDE26830D 12W Led Hid Repl 30K Med Base 1700LM

Keystone Technologies

| | |
|------------------|--|
| Catalog Number | L12HIDE26830D |
| Manufacturer | Keystone Technologies |
| Description | Led Hid Replacement Lamp, 12W, E26 Base, 3000K, 120-277V Input, Directdrive |
| Weight per unit | 0.6400 (lbs/each) |
| Product Category | Led Specialty Lamps & Modules |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 360 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | IP64 |
| lumens | 1620 |
| Nominal Length | N/A |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 12 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | E26 |
| color rendering index (cri) | >80 Deg |
| color temperature | 3000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|--|
| Construction | N/A |
| Description | 12W LED HID REPL 30K MED BASE 1700LM |
| extra long description | Key KT-LED12HID-E26-830-D-DP 12W, 1 |
| Long Description | LED HID REPLACEMENT LAMP, 12W, E26 BASE, 3000K, 120-277V INPUT, DIRECTDRIVE |
| Product Type | 12W, 1700 Lumen, 50W MH Equiv., IP64, Medium Base |

Manufacturer Information

| | |
|---------------------------|--------------------------|
| Brand | Keystone |
| GTIN | 00890949019399 |
| Manufacturers Part Number | KT-LED12HID-E26-830-D-DP |
| UPC | 890949019399 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 16

Weight Per each 0.64

Uses, Certifications, and Standards

Energy Star Y