



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L12T836GC840DX2 12W Led T8 36" 40K Line DBL/SNGL Ended 1450LM *Keystone Technologies*

Catalog Number	L12T836GC840DX2
Manufacturer	Keystone Technologies
Description	12W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 3, 4000K, Direct Drive, Single or Double Ended
Weight per unit	0.5600 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1500
Nominal Length	36 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	5
Wattage	12
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	N/A
Description	12W LED T8 36" 40K LINE DBL/SNGL ENDED 1450LM
extra long description	Key KT-LED12T8-36GC-840-DX2-CP 12W,
Long Description	12W LED T8 TUBE, SHATTER-PROOF COATED GLASS, 120-277V INPUT, 3, 4000K, DIRECT DRIVE, SINGLE OR DOUBLE ENDED
Product Type	12W, 1450 Lumen, 3', 240' Beam Angle, Ballast Bypass, DLC 4.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00890949019221
Manufacturers Part Number	KT-LED12T8-36GC-840-DX2-CP
UPC	890949019221

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.56

Uses, Certifications, and Standards

Energy Star	Y
-------------	---