



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L14.5T848GC840DF KT-LED14.5T8-48GC-840-D-Fdim *Keystone Technologies*

Catalog Number	L14.5T848GC840DF
Manufacturer	Keystone Technologies
Description	14.5W Led T8 Tube, Triac Dimmable, Shatter-Proof Coated Glass, 4, 4000K, 120V Input, Direct Drive
Weight per unit	0.6900 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120V
ip rating	N/A
lumens	1900
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	14.5
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	KTLED145T848GC840DFDIM
extra long description	Key KT-LED14.5T8-48GC-840-D-FDIM-CP
Long Description	14.5W LED T8 TUBE, TRIAC DIMMABLE, SHATTER-PROOF COATED GLASS, 4, 4000K, 120V INPUT, DIRECT DRIVE
Product Type	14.5W, 1900 Lumen, 4', 240' Beam Angle, Ballast Bypass, Phas



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654113227
Manufacturers Part Number	KT-LED14.5T8-48GC-840-D-FDIM-C
UPC	843654113227

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	------------------------------------------------------------------

## Packaging

Carton	20
Weight Per each	0.69

## Uses, Certifications, and Standards

Energy Star	N
-------------	---