**legrand**<sup>®</sup> designed to be better.

L1420P

# 20 Amp NEMA Plug L1420 -Black Back, White Front Body

L1420P



Turnlok Plug 4wire 20amp 125/250v



- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

# specifications

#### **General Info**

Color: Black, White Type: Plug

ov features & benefits

#### Number Of Wires: 4

#### Listing Agencies/Third Party Information

CSA Standard: Yes Federal Spec: Yes Fed Spec Number: WC596 UL Listing No: 498 UL Standard: Yes UN SPS C: 39121403

## Dimensions

Diameter U S: 2.20" Length U S: 3.75"

# **Technical Information**

Amps: 20 Amp NEMA Configuration Number: L1420 Volts: 125/250V Volts A C: 125/250

### **Buy American Act Compliance**

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant