



## 20 AMP NEMA L1420 SINGLE RECEPTACLE

L1420R | Pass & Seymour

#### **FEATURES & BENEFITS**

Turnlok Single Receptacle 4wire 20amp 125/250v



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 #10 AWG.

#### **SPECIFICATIONS**

### **GENERAL INFO**

Type: Single Receptacles Number Of Wires: 4

## LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes Federal Spec: Yes UL Listing No: 498 UL Standard: Yes UN SPSC: 39121403

## **DIMENSIONS**

Depth (US): 1.19" Height (US): 3.28" Width (US): 1.61"

# **TECHNICAL INFORMATION**

Amps: 20A

NEMA Configuration Number: L1420

Volts: 125/250V Volts (AC): 125/250

# **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

