



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604



L1430C LKG Conn, 30A 125/250V, Hub Pro *Hubbell Wiring Devices*

Catalog Number	L1430C
Manufacturer	Hubbell Wiring Devices
Description	Select Spec Twist-Lock® Commercial/Industrial Female Connector Body, 30A 125/250V, 3-Pole 4-Wire Grounding, L14, Screw Terminal
Weight per unit	0.1280 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
connection	Screw Terminals
Current Rating	30
insulation	Insulated Body
Material	COMPOSITE
Number of Conductors	4-Wire Grounding
pallet quantity	2400
Poles	3-Pole
Voltage Rating	125/250

Material, Color, and Finish

Color	Black;White
-------	-------------

Dimensions and Weight

Size	Standard
------	----------

Descriptions

Description	LKG CONN, 30A 125/250V, HUB PRO
extra long description	HWDK L1430C LKG CONN, 30A 125/250V,
Long Description	SELECT SPEC Twist-Lock® Commercial/Industrial Female Connector Body, 30A 125/250V, 3-Pole 4-Wire Grounding, L14,Screw Terminal
Product Type	LKG Conn, 30A 125/250V, Hub Pro
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585650067
Manufacturers Part Number	L1430C
UPC	783585650067

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Hubbell Pro



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604

Packaging

Carton	1
Package	10
Weight Per each	0.128

Uses, Certifications, and Standards

Application	Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L14-30R
standard	NEMA WD1 and WD5, UL498