



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1430FI Flanged Inlet 4W 30A 125/250V T/L *Pass & Seymour/Legrand*

Catalog Number	L1430FI
Manufacturer	Pass & Seymour/Legrand
Description	Locking Device Turnlock Flanged Inlet, 30 A, 125/250 V Ac, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 3.12 In;0.225 to 1.150 In (Cord) Diameter, Flanged, 1.75 In Length, #18 to #8 Awg Wire Size, Impact and Corrosion Resistant, 0.26 LB
Weight per unit	0.2640 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
Poles	2

Material, Color, and Finish

Color	Black&White
-------	-------------

Dimensions and Weight

Size	3.1 in
------	--------

Descriptions

Description	FLANGED INLET 4W 30A 125/250V T/L
extra long description	P&S L1430FI FLANGED INLET 4W 30A 12

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007143027
Manufacturers Part Number	L1430FI
UPC	785007143027

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlock Flanged Inlet

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.264

Uses, Certifications, and Standards

Mounting	Flanged Inlet
standard	CULUS, UL 498