



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L15T848GC865DX2G 15W Led T8 48" 65K DBL/SNGL Ended Coated Glass G2 *Keystone Technologies*

Catalog Number	L15T848GC865DX2G
Manufacturer	Keystone Technologies
Description	15W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 4, 6500K, Direct Drive, Single or Double Ended
Weight per unit	0.6600 (lbs/each)
Product Category	Shape & Circular Lamps

Descriptions

Description	15W LED T8 48" 65K DBL/SNGL ENDED COATED GLASS G2
extra long description	Key KT-LED15T8-48GC-865-DX2-CP 15W,
Long Description	15W LED T8 TUBE, SHATTER-PROOF COATED GLASS, 120-277V INPUT, 4, 6500K, DIRECT DRIVE, SINGLE OR DOUBLE ENDED
Product Type	15W, 2000 Lumen, 4', 240' Beam Angle, Ballast Bypass- DLC 4.

Manufacturer Information

Brand	Keystone
GTIN	00890949016350
Manufacturers Part Number	KT-LED15T8-48GC-865-DX2 /G2
UPC	890949016350

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.66