



## 20 AMP NEMA L1820 SINGLE RECEPTACLE

L1820R | [Pass & Seymour](#)

### FEATURES & BENEFITS

Receptacle Single 4wire 20amp 120/208volt Turnlok



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### SPECIFICATIONS

#### GENERAL INFO

Type: Single Receptacles  
Number Of Wires: 4

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
Federal Spec: Yes  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403

#### DIMENSIONS

Depth (US): 1.19"  
Length (US): 3.28"  
Width (US): 1.61"

## TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L1820

Volts: 120/280V

Volts (AC): 120/280

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





## 20 AMP NEMA L1820 SINGLE RECEPTACLE

L1820R | [Pass & Seymour](#)

### FEATURES & BENEFITS

Receptacle Single 4wire 20amp 120/208volt Turnlok



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### SPECIFICATIONS

#### GENERAL INFO

Type: Single Receptacles  
Number Of Wires: 4

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
Federal Spec: Yes  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403

#### DIMENSIONS

Depth (US): 1.19"  
Length (US): 3.28"  
Width (US): 1.61"

## TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L1820

Volts: 120/280V

Volts (AC): 120/280

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

