



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L25T848G835DX2 25W Led T8 48" 35K DBL/SNGL Ended 3000LM *Keystone Technologies*

Catalog Number	L25T848G835DX2
Manufacturer	Keystone Technologies
Description	25W Led T8 Tube, Glass Construction, 4FT, 3500K, 120-277V Input, 25 PCS Carton, Direct Drive Single or Double Ended
Weight per unit	0.6600 (lbs/each)
Product Category	20201130081610

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	2900
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	5
Wattage	25
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	3500
housing color	N/A

Descriptions

Construction	Frosted Glass
Description	25W LED T8 48" 35K DBL/SNGL ENDED 3000LM
extra long description	Key KT-LED25T8-48G-835-DX2-CP 25W,
Long Description	25W LED T8 TUBE, GLASS CONSTRUCTION, 4FT, 3500K, 120-277V INPUT, 25 PCS CARTON, DIRECT DRIVE SINGLE OR DOUBLE ENDED
Product Type	25W, 3000 Lumen, 4' 240' Beam Angle, Ballast Bypass, DLC 4.0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654123219
Manufacturers Part Number	KT-LED25T8-48G-835-DX2-CP
UPC	843654123219

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.66

Uses, Certifications, and Standards

Energy Star	N
-------------	---