



20 AMP NEMA L520 SINGLE RECEPTACLE

L520R | Pass & Seymour

FEATURES & BENEFITS

Turnlok Receptacle Single, 2pole 3wire, 20amp 125v





- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 #10 AWG.

SPECIFICATIONS

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes Federal Spec: Yes UL Listing No: UL498 UL Standard: Yes UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.19" Height (US): 3.28" Width (US): 1.61"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L520

Volts: 125V Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

