



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1800 S. May Ave.
73108-0000, OK Oklahoma City
Phone: 405-896-3723
Fax: 405-272-3057



L620R Turnlok Recept SGL 3W 20A 250V

Pass & Seymour/Legrand

Catalog Number	L620R
Manufacturer	Pass & Seymour/Legrand
Description	Turnlock Single Receptacle, 20 A, 250 V Ac, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back Wire Connection, Receptacle, 1.61 In Length, 1.19 In Width, 3.28 In Height, Nylon Material, Black, Impact Resistant, 0.2200 LB
Weight per unit	0.2100 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
indoor/outdoor	Indoor
Outlet Type	Indoor, Commercial
Poles	2
Voltage	250.0 V
Wall Plate Included	NO
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	TURNLOK RECP SGL 3W 20A 250V
extra long description	P&S L620R TURNLOK RECEPT SGL 3W 20A

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007262056
Manufacturers Part Number	L620R
UPC	785007262056

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.21



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1800 S. May Ave.
73108-0000, OK Oklahoma City
Phone: 405-896-3723
Fax: 405-272-3057

Uses, Certifications, and Standards

Mounting	Receptacle
Operating Temperature	-40°-75°C
standard	CULUS, UL 498