



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L720R R SGL 3W 20A 277V T/L

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | L720R |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Receptacle Single 3-Wire 20A 277V Turnlok Registered |
| Weight per unit | 0.2205 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|---------|
| amperage rating | 20 |
| Material | Nylon |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage | 277.0 V |
| Voltage Rating | 277 |
| Wire Size | 4 |

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | R SGL 3W 20A 277V T/L |
| extra long description | P&S L720R R SGL 3W20A277V T/L |
| Long Description | Receptacle Single 3-Wire 20A 277V Turnlok Registered |
| Product Type | R SGL 3W20A277V T/L |
| Special Features | Locking Device, impact resistant |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007272055 |
| Manufacturers Part Number | L720-R |
| UPC | 785007272055 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type | Turnlock Single Receptacle |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.2205 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|---------------------------------|
| Application | Industrial Spec Grade |
| Mounting | Receptacle |
| nema rating | L7-20R |
| standard | FEDSPEC, CULUS, UL 498, FEDSPEC |