



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LB250DCG 2-1/2" LB FM5 Cond BC&G *Appleton/Oz Gedney*

Catalog Number	LB250DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Aluminum Threaded For Rigid Conduit and Imc, Type LB, Set Screw, Material: Conduit Body: Diecast, Copperfree Aluminum/Epoxy Powder Coat, Cover: Stamped Aluminum, Natural Finish, Gasket: Neoprene, UI Standard: 514A, Trade Size: 2-12
Weight per unit	4.0 (lbs/each)
Product Category	Alum

### Features

Material	Die Cast Aluminum
----------	-------------------

### Material, Color, and Finish

Finish	Epoxy Powder Coat;Other
--------	-------------------------

### Dimensions and Weight

Height	6.03
Hub Size	3
Length	13.14
Width	4.33

### Descriptions

Description	2-1/2" LB FM5 COND BC&G
extra long description	EGS LB250DCG 2-1/2 THD ALUM LB BDY
Long Description	EMT Conduit Bodies, Aluminum Threaded for rigid conduit and IMC, Type LB, Set Screw, Material: Conduit body: diecast, copperfree aluminum/epoxy powder coat, Cover: stamped aluminum, natural finish, Gasket: neoprene, UL Standard: 514A, Trade Size: 2-12
Product Type	2-1/2 THD Alum LB Bdy CVR GSKT
Special Features	2-1/2 IN Trade Size, Type LB Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #4/0 AWG, Volume 153.00 IN <sup>3</sup> , For Use With Rigid and IMC Conduit, Furnished With Cover and Gasket

### Manufacturer Information

Brand	Appleton
GTIN	00687855001293
Manufacturers Part Number	LB250DCG
UPC	687855001293



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body

## Packaging

Carton	1
Weight Per each	4

## Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A