



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LBY35SA 1" 90D Conduit Elbow

Crouse-Hinds

Catalog Number	LBY35SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Lby Elbow, Rigid/Imc, Copper-Free Aluminum, 90°, 1"
Weight per unit	0.5900 (lbs/each)
Product Category	Aluminum

Features

connection	Threaded
dimensions	2.5000 IN X 2.5000 IN X 3.2500 IN

Material, Color, and Finish

Finish	Untreated
--------	-----------

Descriptions

Description	1" 90D CONDUIT ELBOW
extra long description	CRS-H LBY35 SA 1 LBY AL ELBOW CVR
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series Condulet LBY elbow, Rigid/IMC, Copper-free aluminum, 90°, 1"
Product Type	1 Lby Al Elbow CVR

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274277073
Manufacturers Part Number	LBY35 SA
UPC	782274277073

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	ELBOW

Packaging

Carton	1
Package	5
Weight Per each	0.59



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2