



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCD1014AFL #10AWG 2-H 90D Comp Lug *Panduit Corporation*

Catalog Number	LCD1014AFL
Manufacturer	Panduit Corporation
Description	Two-Hole, Standard Barrel Lug With Window, #10 Awg Wire, 1/4 Stud Hole, .63 Hole Spacing, 90° Angle Tongue.
Weight per unit	0.0142 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Tin-Plated Copper
media	Yes
Number of Holes	2
Stud Size	1/4

Dimensions and Weight

Size	#14 — #10 AWG Code STR, #12 — #10 AWG Code SOL
------	--

Descriptions

Description	#10AWG 2-H 90D COMP LUG
extra long description	PAN LCD10-14AF-L Pan-Lug™ LCD10-14A
Long Description	Two-hole, standard barrel lug with window, #10 AWG wire, 1/4 stud hole, .63 hole spacing, 90° angle tongue.
Product Type	Pan-Lug™ LCD10-14AF-L Comp. Lug, 10, Tin PLT Copper, Two 0.2
Special Features	Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 V

Manufacturer Information

Brand	PANDUIT
GTIN	00074983973767
Manufacturers Part Number	LCD1014AFL
UPC	074983973767

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Compression Lug

Packaging

Carton	1
Package	50
Weight Per each	0.0142

Uses, Certifications, and Standards

Mounting	7/16
standard	UL listed to 486A-486B File #E52164 and CSA certified C22.2 No. 65-13