



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCR6159FSE010MW *Delisted* 6" 16W Led Tunable 27K/3K/35K/4K/5K *Cooper Lighting Solutions*

Catalog Number	LCR6159FSE010MW
Manufacturer	Cooper Lighting Solutions
Description	6" All- Purpose Round Led Module, 1500 Lumens, 90 Cri Minimum, Field Selectable CCT, Unv 120 - 277V, 0-10V Dimming, Matte White Finish
Weight per unit	1.5 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.067A at 277V
Lamp Type	LED
Voltage Rating	120-277V

Descriptions

Description	*DELISTED* 6" 16W LED TUNABLE 27K/3K/35K/4K/5K
extra long description	CLS LCR6159FSE010MW 6" LCR, 1500 LM
Long Description	6" all- purpose round LED module, 1500 lumens,90 CRI minimum, field selectable CCT,UNV 120 - 277V, 0-10V dimming,Matte white finish
Product Type	6" LCR, 1500 LM, RND, 120-277V, 0-10V
Special Features	Canless Direct Mount - does not require recessed housing or junction box

Manufacturer Information

Brand	HALO
GTIN	00080083890026
Manufacturers Part Number	LCR6159FSE010MW
UPC	080083890026

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	6" LCR

Packaging

Carton	1
Package	4
Weight Per each	1.54

Uses, Certifications, and Standards

Application	lighting
standard	California Title 24;ENERGY STAR Qualified;IECC Compliant;RoHS Compliant