



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LD12T5HE36GC840D \*Delisted\* 12W 120-277V 40K 3' Led T5 *Keystone Technologies*

Catalog Number	LD12T5HE36GC840D
Manufacturer	Keystone Technologies
Description	12W Led T5 Tube, Shatter-Proof Coated Glass, Direct Drive, Single or Double Ended, 3 FT., 4000K, 80+Cri, 120-277V Input
Weight per unit	0.4000 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1400
Nominal Length	36 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	5
Wattage	12
Wire Type	N/A

### Material, Color, and Finish

Base Type	G5
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	12W 120-277V 40K 3' LED T5
extra long description	Key KT-LED12T5HE-36GC-840-DX2 12W,
Long Description	12W LED T5 Tube, Shatter-Proof Coated Glass, Direct Drive, Single or Double Ended, 3 ft., 4000K, 80+CRI, 120-277V Input
Product Type	12W, 1400 Lumen, 3', 240' Beam Angle, Ballast Bypass



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654130477
Manufacturers Part Number	KT-LED12T5HE-36GC-840-DX2
UPC	843654130477

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.4

## Uses, Certifications, and Standards

Energy Star	N
-------------	---