




GE
Lighting

65136 - GE LED PAR30

LED12DP30S830/35

 Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26
Bulb Shape	PAR30

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	2050 cd
Lumens per Watt (Efficacy)	63 lm
Nominal Initial Lumen per Watt	63
Rated Beam Spread	35 deg
Initial Lumens-nominal	750 lm
Color Rendering Index-CRI	84
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	65136
Description	LED12DP30S830/35
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168651363
Standard Package GTIN	00043168651363
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168651363
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	12 W