



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED12T8L36FG841B 3' 12W Led T8 41K DBL End Line Volt 120-277V 1450L

*Sylvania-Ledvance*

Catalog Number	LED12T8L36FG841B
Manufacturer	Sylvania-Ledvance
Description	OBS75011 3 FT, Ledlescent Ballast Free Led T8, Frosted Glass, 12W, 120 277V, 82 Cri, 1450 Lumens, 4100K CCT, 50000 Life
Weight per unit	0.4488 (lbs/each)
Product Category	Lighting

### Features

average life	50000
Base	G13
Lamp Type	LED T8
Shape	T8
Wattage	12.00

### Material, Color, and Finish

color rendering index (cri)	82
Style	Tube, double-ended

### Dimensions and Weight

Size	1.02
------	------

### Descriptions

Description	3' 12W LED T8 41K DBL END LINE VOLT 120-277V 1450L
extra long description	SYL LED12T8/L36/FG/841/BF/75011 LED
Long Description	OBS75011 3 ft, LEDlescent Ballast free LED T8, frosted glass, 12W, 120 277V, 82 CRI, 1450 Lumens, 4100K CCT, 50000 life
Product Type	LED12T8L36FG841BF 25/CS 1/Sku

### Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135750113
Manufacturers Part Number	LED12T8/L36/FG/841/BF/75011
UPC	046135750113

### Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

### Packaging

Carton	1
Package	25
Weight Per each	0.4488

### Uses, Certifications, and Standards

standard	RoHS
----------	------