



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED15ET8850V6P *Delisted* 15W Led T8 48" 50K Glass 1800LM 36000HR

Ge By Current Lamps

Catalog Number	LED15ET8850V6P
Manufacturer	Ge By Current Lamps
Description	35911 Led Tube Light, 15 W, 120 V, 45.7 A, 1800 LM, 48 In., T8, 36000 H Average Life, Plug-In, Linear Fluorescent Fixture, 80+ Color Rendering Index (Cri), 5000 K Color Temperature
Weight per unit	0.8000 (lbs/each)
Product Category	Shape & Circular Lamps

Features

amperage rating	45.7
average life	36000
Fixture Type	Linear Fluorescent Fixture
lumens	1800
Shape	T8
Voltage Rating	120
Wattage	15

Material, Color, and Finish

color rendering index (cri)	80+
-----------------------------	-----

Dimensions and Weight

Size	48
------	----

Descriptions

Description	*DELISTED* 15W LED T8 48" 50K GLASS 1800LM 36000HR
extra long description	GEL LED15ET8/850-V6P 35911 LED Tube
Long Description	35911 LED Tube Light, 15 W, 120 V, 45.7 A, 1800 LM, 48 in., T8, 36000 H average life, Plug-In, Linear Fluorescent Fixture, 80+ color rendering index (cri), 5000 K color temperature
Product Type	35911 Led Tube Lamps
Special Features	Features: Each LED tube is outfitted with an internal GE driver, Easy disposal, Non-Hazardous Waste, No UV

Manufacturer Information

Brand	GE Current
GTIN	00043168359115
Manufacturers Part Number	LED15ET8/850-V6P
UPC	043168359115

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	LED Tube Light



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.8

Uses, Certifications, and Standards

Application	Damp Location
Mounting	Plug-in
standard	UL