



# LED T8 Instant Start Ballast Compatible

T8 LED tubes that are direct replacements for 32W fluorescent lamps used with Instant Start Ballasts.

## Limitless options for the following applications:

- Offices
- Restaurants
- Retail Stores
- Lobbies
- Schools
- Hospitals

## Great features and benefits:

- >40% Energy Savings
- Long life: 50,000 hours
- No rewiring of fixture - just replace fluorescent lamp with LED lamp
- Instant on/off
- Shatterproof - no glass
- 30K, 35K, 41K & 50K color temperatures
- No Mercury
- 5 year warranty

Direct8™  
LED



LED T8



LED

we know light.™

TCP

325 Campus Dr. | Aurora, Ohio 44202 | P: 800-324-1496 | tcp.com

©TCP JAN 2015/54323



# LED T8 Instant Start Ballast Compatible


**LED** 50,000 Hours average rated life

### Applications:



T8 LED tubes that are direct replacements for 32W fluorescent lamps used with Instant Start Ballasts.\*

### Features

>40% Energy Savings	Shatterproof - no glass
Long life - 50,000 hours	No Mercury
Instant on/off	5 year warranty
No rewiring of fixture - just replace fluorescent lamp with LED lamp	



**Direct8**<sup>TM</sup>  
LED



Warranties and Certifications:	Item #	Description	DLC QPL	Wattage			Lamp Lumens			Base	CCT	CRI	R9
				LBF (0.78)	NBF (0.88)	HBF (1.18)	LBF (0.78)	NBF (0.88)	HBF (1.18)				
<b>5 YEAR WARRANTY</b> 	LED15T84IS30K	LED 15W Instant Start Compatible 4 Foot T8 - 3000K		13.2	14.9	20.0	1396	1575	2112	G13	3000K	82	>0
	LED15T84IS35K	LED 15W Instant Start Compatible 4 Foot T8 - 3500K		13.2	14.9	20.0	1418	1600	2145	G13	3500K	82	>0
	LED15T84IS41K	LED 15W Instant Start Compatible 4 Foot T8 - 4100K	★	13.2	14.9	20.0	1463	1650	2213	G13	4100K	82	>0
	LED15T84IS50K	LED 15W Instant Start Compatible 4 Foot T8 - 5000K	★	13.2	14.9	20.0	1507	1700	2280	G13	5000K	82	>0

\* Please refer to [www.tcp.com](http://www.tcp.com) for Instant Start Ballast Compatibility.