



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED16.5PAR38HDD 16.5W Led PAR38 27K 40D *Sylvania-Ledvance*

Catalog Number	LED16.5PAR38HDD
Manufacturer	Sylvania-Ledvance
Description	OBS78354 Led PAR38, 16.5W, Dimmable, 91CRI, 1250 Lumen, 2700K, 25000 Life
Weight per unit	1.2 (lbs/each)
Product Category	Led Parabolic Reflector Par SH

Features

average life	25000
Base	E26 Medium
Lamp Type	LED PAR38
lumens	1,250
Shape	PAR38
Voltage	120.00 V
Voltage Rating	120.00
Wattage	16.50

Material, Color, and Finish

color rendering index (cri)	91
Style	PAR38-shape

Dimensions and Weight

Size	4.74
------	------

Descriptions

Description	16.5W LED PAR38 27K 40D
extra long description	SYL LED16.5PAR38/HD/DIM/927/FL40/78
Long Description	OBS78354 LED PAR38, 16.5W, Dimmable, 91CRI, 1250 Lumen, 2700K, 25000 life
Product Type	LED16.5PAR38HDDIM927FL40 6/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135783548
Manufacturers Part Number	LED16.5PAR38/HD/DIM/927/FL40/7
UPC	046135783548

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
----------------------	---------------------

Packaging

Carton	1
Package	6
Weight Per each	1.1566



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

FCC
