



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED16A19DIM0840U 16W Led A19 40K Dim 1600LM *Sylvania-Ledvance*

Catalog Number	LED16A19DIM0840U
Manufacturer	Sylvania-Ledvance
Description	Led A19, 16W, Dimmable, 80CRI, 1600 Lumen, 4000K, 15000 Life, E26 Medium Base, Frosted Finish
Weight per unit	0.8310 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	E26 Medium
Lamp Type	LED A19
lumens	1,600
Shape	A19
Voltage	120.00 V
Voltage Rating	120.00
Wattage	16.00

Material, Color, and Finish

color rendering index (cri)	80
Style	A-shape

Dimensions and Weight

Size	2.56
------	------

Descriptions

Description	16W LED A19 40K DIM 1600LM
extra long description	SYL LED16A19DIMO840URP/41192 LED16A
Long Description	LED A19, 16W, Dimmable, 80CRI, 1600 Lumen, 4000K, 15000 Life, E26 Medium Base, FROSTED Finish
Product Type	LED16A19DIMO840URP 6/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135411922
Manufacturers Part Number	LED16A19DIMO840URP/41192
UPC	046135411922

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
----------------------	------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.831

Uses, Certifications, and Standards

standard	RoHS
----------	------