




GE  
Lighting

**14074 - LED16DA21/827**

GE LED A21



**GENERAL CHARACTERISTICS**

Lamp Type	Replacement Lamps - A-line
Bulb	A21
Base	Medium Screw (E26)
Additional Info	GE Life Rating is based on 70% Lumen Maintenance
Bulb Shape	A-21
Color	White
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	100.0 W
Lamp Type	A-21
Life in Years (NOM)	22.8
Rated Life (NOM)	25000.0 h

**PHOTOMETRIC CHARACTERISTICS**

Color Rendering Index (CRI) (NOM)	80.0
Color Temperature (NOM)	2700.0 K
Initial Lumens (NOM)	1600.0
Lumens per Watt (Efficacy) (NOM)	100.0 lm
Nominal Initial Lumens per Watt (NOM)	100.0

**ELECTRICAL CHARACTERISTICS**

Estimated Energy Cost per Year (NOM)	1.93
Voltage (NOM)	120.0
Wattage (NOM)	16.0

**DIMENSIONS**

Bulb Diameter (DIA) (NOM)	78.0 mm
Maximum Overall Length (MOL) (NOM)	134.9 mm

**PRODUCT INFORMATION**

Product Code	14074
Description	LED16DA21/827
Standard Package	Case
Standard Package GTIN	10043168140741
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168140744