



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED16PAR38DIM850 16W Led PAR38 50K 1300LMP *Sylvania-Ledvance*

Catalog Number	LED16PAR38DIM850
Manufacturer	Sylvania-Ledvance
Description	Led PAR38, 16W, Dimmable, 82CRI, 1300 Lumen, 5000K, 15000 Life, E26 Medium Base
Weight per unit	1.4 (lbs/each)
Product Category	Led Parabolic Reflector Par SH

Features

average life	15000
Base	E26 Medium
Lamp Type	LED PAR38
lumens	1,300
Shape	PAR38
Voltage	120.00 V
Voltage Rating	120.00
Wattage	16.00

Material, Color, and Finish

color rendering index (cri)	82
Style	PAR38-shape

Dimensions and Weight

Size	4.8
------	-----

Descriptions

Description	16W LED PAR38 50K 1300LMP
extra long description	SYL LED16PAR38DIM850FL4013YGLWRP/74
Long Description	LED PAR38, 16W, Dimmable, 82CRI, 1300 Lumen, 5000K, 15000 Life, E26 Medium Base
Product Type	LED16PAR38DIM850FL4013YGLWRP 6/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135749506
Manufacturers Part Number	LED16PAR38DIM850FL4013YGLWRP/7
UPC	046135749506

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
----------------------	---------------------

Packaging

Carton	6
Weight Per each	1.4235



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS
