



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED17T8L48841BF *Delisted* 17W Led T8 48" 41K DBL 120-277V

Sylvania-Ledvance

Catalog Number	LED17T8L48841BF
Manufacturer	Sylvania-Ledvance
Description	OBSL48/FG/841/BFG2 4 FT, Ledlescent Ballast Free Led T8, Frosted Glass, 17W, 120 277V, 82 Cri, 2200 Lumens, 4100K CCT, 50000 Life
Weight per unit	0.6712 (lbs/each)
Product Category	Shape & Circular Lamps

Features

average life	50000
Base	G13
Lamp Type	LED T8
lumens	2,200
Voltage	120.00 - 277.00 V
Wattage	17.00

Material, Color, and Finish

color rendering index (cri)	82
Style	Tube, double-ended

Dimensions and Weight

Size	1.02
------	------

Descriptions

Description	17W LED T8 48" 41K DBL 120-277V
extra long description	SYL LED17T8/L48/FG/841/BF/75026 LED
Long Description	OBSL48/FG/841/BFG2 4 ft, LEDlescent Ballast free LED T8, frosted glass, 17W, 120 277V, 82 CRI, 2200 Lumens, 4100K CCT, 50000 life

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135750267
Manufacturers Part Number	LED17T8/L48/FG/841/BF/75026
UPC	046135750267

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Package	25
Weight Per each	0.6712



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS
