



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED17T8L48FG84 *Delisted* 17W Led T8 48" 41K DBL 120-277V *Sylvania-Ledvance*

Catalog Number	LED17T8L48FG84
Manufacturer	Sylvania-Ledvance
Description	OBS41456 4FT, Ledlescenttm Ballast Free Dimmable Led T8, Frosted Glass, 17W, 120 277V, 82 Cri, 2200 Lumens, 4100 K, 50000 HRS Life
Weight per unit	0.4890 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED T8
lumens	2,200
Voltage	120.00 - 277.00 V

Descriptions

Description	*DELISTED* 17W LED T8 48" 41K DBL 120-277V
extra long description	SYL M841BFG2-LED17T8/L48/FG/841/BFG
Long Description	OBS41456 4ft, LEDlescentTM Ballast Free Dimmable LED T8, frosted glass, 17W, 120 277V, 82 CRI, 2200 Lumens, 4100 K, 50000 hrs Life
Product Type	LED17T8L48FG841BFG2 25/CS 1/Sku

Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135414565
Manufacturers Part Number	LED17T8/L48/FG/841/BF/41456
UPC	046135414565

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Package	25
Weight Per each	0.489