



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED18D380W384040 18W Led PAR38 40K Wet Loc 40 Deg

Ge By Current Lamps

Catalog Number	LED18D380W384040
Manufacturer	Ge By Current Lamps
Description	Led PAR38 Lamp, 40 ° Beam Angle, 81, 4000 K, 1700 LM Brightness (Lumens), 18 W, 120 V, White, 25000 H Average Life, E26 Medium Screw-In Base, Dimmable, 5.31 In Length, 150 W
Weight per unit	1.2 (lbs/each)
Product Category	Led Parabolic Reflector Par SH

Features

average life	25000
Base	Medium Screw
lumens	1700

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Diameter	40
Overall Length	5.31

Descriptions

Description	18W LED PAR38 40K WET LOC 40 DEG
extra long description	GEL LED18D38OW3840/40 93172 Directi

Manufacturer Information

Brand	GE Current
GTIN	00043168931724
Manufacturers Part Number	LED18D38OW3840/40
UPC	043168931724

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
----------------------	---------------------

Packaging

Carton	1
Package	6
Weight Per each	1.21