



DIRECT DRIVE LED
LINE VOLTAGE T8 TUBES

KT-LED18T8-U6GC-840-D

U-BEND T8 LED LAMP

DESCRIPTION

18W T8 U-Bend LED | 4000K | >80 CRI | High Efficiency



LAMP TYPE: U-Bend
BULB TYPE: T8 LED
BASE TYPE: G13 (Medium Bi-Pin)
WATTAGE: 18W
COLOR TEMPERATURE: 4000K
COLOR RENDERING INDEX (CRI): >80
WARRANTY: 5 Years



PRODUCT FEATURES

- Replacement for Conventional Fluorescent Lamp
- UL Classified; Listed on DLC Qualified Product List
- 50,000+ Hour Lifetime
- Approximately 40% More Energy Efficient than Standard F32T8 Lamps
- Environmentally Friendly: No Mercury Used
- Integral Driver (Isolated) Eliminates the Need for an External Ballast or Driver
- Instant Startup
- Frosted Lens Eliminates Pixelation
- Operating Temperature: -20°C/-4°F to 45°C/113°F
- 110+ Lumens per Watt (Bare Lamp Efficacy)
- Suitable for Dry and Damp Locations
- Improved Lamp Durability with Shatterproof Coated Glass
- NSF Listed: NSF/ANSI Standard 2 - Food Equipment

OPERATING SPECIFICATIONS


ELECTRICAL AND PERFORMANCE CHARACTERISTICS

Input Voltage	CRI	Bare Lamp Wattage	Nominal Lamp Lumens	Beam Angle	Nominal Bare Lamp Efficacy	Power Factor	Max. THD
120-277V	>80	18W	2150	220°	119 lm/W	>0.9	20%

RATED LIFE

L70 (Hours)	50,000
-------------	--------

POLAR CANDELA DISTRIBUTION



Located at Horizontal Angle = 0,
Vertical Angle 0

1. Violet Vertical Plane through Horizontal
Angles (90-270)

2. Green Vertical Plane through Horizontal
Angles (0-180)

Beam Angle: 220°

Visible Light Area: 325°




KT-LED18T8-U6GC-840-D

U-BEND T8 LED LAMP

WIRING

Re-wire fixture as show below.



Typical Non-Shunted Lampholder


Connect wires directly to these terminals

CAUTION:
Use only non-shunted lampholders.

Do not install product in a fixture with shunted lampholders (found in all fixtures using instant start ballasts). If the current lampholders are shunted, remove them and replace them with non-shunted lampholders. Make new connections directly to terminals as indicated above.

Keystone can provide any style replacement lampholders. Call us at 800-464-2680.

PHYSICAL CHARACTERISTICS



LAMP DIMENSIONS

A (Illuminated Length)	20.20"
B (Body Length)	22.25"
C (Diameter)	1.00"
D (Width)	6.00"
Nominal Length	6" U-Bend
Base Type	G13 (Medium Bi-Pin)

ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED18T8-U6GC-840-D-CP	Carton Pack (Egg Crate Packaging)	12	Quick Ship

CATALOG NUMBER BREAKDOWN

KT-LED18T8-U6GC-840-D-CP





KT-LED18T8-U6GC-840-D

U-BEND T8 LED LAMP

DESCRIPTION

18W T8 U-Bend LED | 4000K | >80 CRI | High Efficiency



LAMP TYPE: U-Bend
BULB TYPE: T8 LED
BASE TYPE: G13 (Medium Bi-Pin)
WATTAGE: 18W
COLOR TEMPERATURE: 4000K
COLOR RENDERING INDEX (CRI): >80
WARRANTY: 5 Years



PRODUCT FEATURES

- Replacement for Conventional Fluorescent Lamp
- UL Classified; Listed on DLC Qualified Product List
- 50,000+ Hour Lifetime
- Approximately 40% More Energy Efficient than Standard F32T8 Lamps
- Environmentally Friendly: No Mercury Used
- Integral Driver (Isolated) Eliminates the Need for an External Ballast or Driver
- Instant Startup
- Frosted Lens Eliminates Pixelation
- Operating Temperature: -20°C/-4°F to 45°C/113°F
- 110+ Lumens per Watt (Bare Lamp Efficacy)
- Suitable for Dry and Damp Locations
- Improved Lamp Durability with Shatterproof Coated Glass
- NSF Listed: NSF/ANSI Standard 2 - Food Equipment

OPERATING SPECIFICATIONS


ELECTRICAL AND PERFORMANCE CHARACTERISTICS

Input Voltage	CRI	Bare Lamp Wattage	Nominal Lamp Lumens	Beam Angle	Nominal Bare Lamp Efficacy	Power Factor	Max. THD
120-277V	>80	18W	2150	220°	119 lm/W	>0.9	20%

RATED LIFE

L70 (Hours)	50,000
-------------	--------

POLAR CANDELA DISTRIBUTION



- Located at Horizontal Angle = 0,
Vertical Angle 0
1. Violet Vertical Plane through Horizontal Angles (90-270)
 2. Green Vertical Plane through Horizontal Angles (0-180)
-
- Beam Angle: 220°**
-
- Visible Light Area: 325°**




KT-LED18T8-U6GC-840-D

U-BEND T8 LED LAMP

WIRING

Re-wire fixture as show below.



Typical Non-Shunted Lampholder


Connect wires directly to these terminals

CAUTION:
Use only non-shunted lampholders.

Do not install product in a fixture with shunted lampholders (found in all fixtures using instant start ballasts). If the current lampholders are shunted, remove them and replace them with non-shunted lampholders. Make new connections directly to terminals as indicated above.

Keystone can provide any style replacement lampholders. Call us at 800-464-2680.

PHYSICAL CHARACTERISTICS



LAMP DIMENSIONS

A (Illuminated Length)	20.20"
B (Body Length)	22.25"
C (Diameter)	1.00"
D (Width)	6.00"
Nominal Length	6" U-Bend
Base Type	G13 (Medium Bi-Pin)

ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED18T8-U6GC-840-D-CP	Carton Pack (Egg Crate Packaging)	12	Quick Ship

CATALOG NUMBER BREAKDOWN

KT-LED18T8-U6GC-840-D-CP

