



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED24T5H0L48FG85 *Delisted* 24W Led T5 Ho 48" 50K DBL End 3500LM *Sylvania-Ledvance*

Catalog Number	LED24T5H0L48FG85
Manufacturer	Sylvania-Ledvance
Description	OBS40611 Led T5HO Ledlescent 4FT, 24W, 82CRI, 3500 Lumen, 5000K, 50000 Life
Weight per unit	0.3090 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	Miniature Bipin
Lamp Type	LED T5HO LEDLESCENT 4FT
lumens	3,500
Shape	T5
Voltage	120.00 - 277.00 V
Wattage	24.00

Material, Color, and Finish

color rendering index (cri)	82
Style	Tube, double-ended

Dimensions and Weight

Size	0.67
------	------

Descriptions

Description	24W LED T5 HO 48" 50K DBL END LINE VOLTAGE 3500LM
extra long description	SYL LED24T5HO/L48/FG/850/BF/40611 L
Long Description	OBS40611 LED T5HO LEDlescent 4ft, 24W, 82CRI, 3500 Lumen, 5000K, 50000 life
Product Type	LED24T5H0L48FG850BF 25/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135406119
Manufacturers Part Number	LED24T5HO/L48/FG/850/BF/40611
UPC	046135406119

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Package	25
Weight Per each	0.309



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

CSA
