



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED4FB11E26927C 4W Led B11 Straight Tip 27K Med Base

Keystone Technologies

Catalog Number	LED4FB11E26927C
Manufacturer	Keystone Technologies
Description	Straight Tip Chandelier Filament Bulb, 40W Equivalent, B11 Shape, E26 Medium Base, 2700K, 90 Cri , Clear
Weight per unit	0.1100 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	360 Deg
Circuit Type	N/A
Input Voltage	120V
ip rating	N/A
lumens	350
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	3
Wattage	4
Wire Type	N/A

Material, Color, and Finish

Base Type	E26
color rendering index (cri)	>90 Deg
color temperature	2700
housing color	N/A

Descriptions

Construction	Clear Glass
Description	4W LED B11 STRAIGHT TIP 27K MED BASE
extra long description	Key KT-LED4FB11-E26-927-C 40W Equiv
Long Description	Straight Tip Chandelier Filament bulb, 40W Equivalent, B11 shape, E26 Medium base, 2700K, 90 CRI , Clear
Product Type	40W Equiv., 4W, 350 Lumen, B11, E26, =90 Cri, Dimmable 27K/3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654123653
Manufacturers Part Number	KT-LED4FB11-E26-927-C
UPC	843654123653

Taxonomies, Classifications, and Categories

Category Description	LED DECORATIVE C, CA, F, G SHAPE LAMPS
----------------------	--

Packaging

Carton	1
Weight Per each	0.11

Uses, Certifications, and Standards

Energy Star	Y
-------------	---