



# Elite A19 A-Lamps

## Omni-Directional and All-Purpose

High efficiency A-Lamps. Light output in all directions to suit many applications.

### Limitless options for the following applications:

- General Lighting
- Floor Lamps
- Ceiling Fixtures
- Table Lamps
- Sconces

### Great features and benefits:

- Energy efficient: Up to 85% more efficient than incandescent alternatives.
- Smooth, uniform dimming; also available as non-dimming.
- Long life: 25,000 hours.
- Similar look and feel as incandescent alternative.
- Excellent color consistency and high color rendering (CRI).
- Available in 2400K, 2700K, 3000K, 4100K and 5000K.
- Fits any installations where a standard A19 bulb is used.
- Rated for totally enclosed fixtures.



All-Purpose A-Lamp



Omni-Directional A-Lamp



LED  
we know light.™

TCP®

325 Campus Dr. | Aurora, Ohio 44202 | P: 800-324-1496 | tcp.com

©TCP SEP 2014/54031




**LED** 25,000 Hours average rated life, 120 Volts

**Applications:**

Ideal for applications where uniform multi-directional light output is required.


- + Table Lamps
- + Floor Lamps
- + Sconces
- + Ceiling Fixtures
- + Decorative Fixtures



**Features**

**Benefits**

Up to 85% less energy than halogen alternatives	Instant energy savings
Long life	Minimizes replacement and maintenance costs
Very low heat generation	Perfect for sensitive display lighting such as art galleries.
Excellent Color Consistency and CRI	Enhances colors of focal point while maintaining uniformity throughout lighting installation from lamp to lamp.
UL approved for damp location	Can be used outdoors when protected from elements. Withstands humidity indoors/outdoors.
Shatter resistant	Lower the risk of injury and breakage
ANSI construction compliant	Fits all A19 installations



**Specifications**

Input Line Voltage:	120 VAC
Input Power	See Chart
Input Line Frequency	50/60HZ
Lamp Life (Rated)	25,000 hrs
Minimum Starting Temp	-30°C
Maximum Operating Temp	40°C
CRI	82



A19 A-Lamp

**Omni-Directional**



- + Best "technical" A-Lamp replacement
- + Based on ENERGY STAR standard for omni-directional lamps.
- + Supported by many utility rebates.

**All-Purpose**



- + Best "value" A-Lamp replacement
- + All-purpose lamp with excellent uniformity within 230 degrees that works well in all A-Lamp fixtures.



**5 YEAR WARRANTY\***

For the most up-to-date specs, please visit [www.tcp.com](http://www.tcp.com)

\*Based on 12 hours use per day





Warranties and Certifications:



5 YEAR WARRANTY\*

For the most up-to-date specs, please visit www.tcp.com

\*Based on 12 hours use per day

60W Equivalent Options

10W A19 Omni-Directional A-Lamp - Dimmable

Item #	Description	Voltage	Wattage	Incandescent Wattage Comparison	Lumens	LPW	CCT	CRI	R9	M.O.L (inches)	Diameter (inches)	Case Quantity
LED10A19D0D24K	10W Omni Dimmable A-Lamp - 2400K	120	10	60	750	75.0	2400K	82	>0	4.3	2.4	12
LED10A19D0D27K	10W Omni Dimmable A-Lamp - 2700K	120	10	60	800	80.0	2700K	82	>0	4.3	2.4	12
LED10A19D0D30K	10W Omni Dimmable A-Lamp - 3000K	120	10	60	825	83.0	3000K	82	>0	4.3	2.4	12
LED10A19D0D41K	10W Omni Dimmable A-Lamp - 4100K	120	10	60	850	85.0	4100K	82	>0	4.3	2.4	12
LED10A19D0D50K	10W Omni Dimmable A-Lamp - 5000K	120	10	60	850	85.0	5000K	82	>0	4.3	2.4	12

10W A19 Omni-Directional A-Lamp - Non Dimmable

LED10A19D0D27K	10W Omni Non Dim A-Lamp - 2700K	120	10	60	800	80.0	2700K	82	>0	4.3	2.4	12
LED10A19D0D30K	10W Omni Non Dim A-Lamp - 3000K	120	10	60	825	83.0	3000K	82	>0	4.3	2.4	12

10W A19 All-Purpose A-Lamp - Dimmable

LED10A19D27K	10W Dimmable A-Lamp - 2700K	120	10	60	800	80.0	2700K	82	>0	4.3	2.4	12
LED10A19D30K	10W Dimmable A-Lamp - 3000K	120	10	60	825	83.0	3000K	82	>0	4.3	2.4	12
LED10A19D41K	10W Dimmable A-Lamp - 4100K	120	10	60	850	85.0	4100K	82	>0	4.3	2.4	12
LED10A19D50K	10W Dimmable A-Lamp - 5000K	120	10	60	850	85.0	5000K	82	>0	4.3	2.4	12

9W A19 All-Purpose A-Lamp - Non Dimmable

LED9A1927K	9W Non Dimmable A-Lamp - 2700K	120	10	60	800	80.0	2700K	82	>0	4.3	2.4	12
LED9A1930K	9W Non Dimmable A-Lamp - 3000K	120	10	60	825	83.0	3000K	82	>0	4.3	2.4	12
LED9A1941K	9W Non Dimmable A-Lamp - 4100K	120	10	60	850	85.0	4100K	82	>0	4.3	2.4	12
LED9A1950K	9W Non Dimmable A-Lamp - 5000K	120	10	60	850	85.0	5000K	82	>0	4.3	2.4	12

40W Equivalent Options

7W A19 Omni-Directional A-Lamp - Dimmable

LED7A19D0D24K	7W Omni Dimmable A-Lamp - 2400K	120	7	40	400	57.0	2400K	82	>0	4.3	2.4	12
LED7A19D0D27K	7W Omni Dimmable A-Lamp - 2700K	120	7	40	450	64.0	2700K	82	>0	4.3	2.4	12
LED7A19D0D30K	7W Omni Dimmable A-Lamp - 3000K	120	7	40	475	68.0	3000K	82	>0	4.3	2.4	12
LED7A19D0D41K	7W Omni Dimmable A-Lamp - 4100K	120	7	40	500	71.0	4100K	82	>0	4.3	2.4	12
LED7A19D0D50K	7W Omni Dimmable A-Lamp - 5000K	120	7	40	500	71.0	5000K	82	>0	4.3	2.4	12

7W A19 Omni-Directional A-Lamp - Non Dimmable

LED7A19D0D27K	7W Omni Non Dim A-Lamp - 2700K	120	7	40	450	64.0	2700K	82	>0	4.3	2.4	12
LED7A19D0D30K	7W Omni Non Dim A-Lamp - 3000K	120	7	40	475	68.0	3000K	82	>0	4.3	2.4	12

7W A19 All-Purpose A-Lamp - Dimmable

LED7A19D24K	7W Dimmable A-Lamp - 2700K	120	7	40	400	57.0	2400K	82	>0	4.3	2.4	12
LED7A19D27K	7W Dimmable A-Lamp - 2700K	120	7	40	450	64.0	2700K	82	>0	4.3	2.4	12
LED7A19D30K	7W Dimmable A-Lamp - 3000K	120	7	40	475	68.0	3000K	82	>0	4.3	2.4	12
LED7A19D41K	7W Dimmable A-Lamp - 4100K	120	7	40	500	71.0	4100K	82	>0	4.3	2.4	12
LED7A19D50K	7W Dimmable A-Lamp - 5000K	120	7	40	500	71.0	5000K	82	>0	4.3	2.4	12

5W A19 All-Purpose A-Lamp - Non Dimmable

LED5A1927K	5W Non Dimmable A-Lamp - 2700K	120	7	40	450	64.0	2700K	82	>0	4.3	2.4	12
LED5A1930K	5W Non Dimmable A-Lamp - 3000K	120	7	40	475	68.0	3000K	82	>0	4.3	2.4	12
LED5A1941K	5W Non Dimmable A-Lamp - 4100K	120	7	40	500	71.0	4100K	82	>0	4.3	2.4	12
LED5A1950K	5W Non Dimmable A-Lamp - 5000K	120	7	40	525	75.0	5000K	82	>0	4.3	2.4	12



# CREATING BEAUTY

TCP has a **20-year history in energy-efficient lighting.**

Thanks to our **cutting edge technology** and deep manufacturing

expertise, we have shipped literally billions of high quality lamps and

our **integrated technology** and manufacturing

provides **expedited time-to-market.** With TCP, you can

count on unique lighting products designed to meet very specific needs –

lighting that transforms your surroundings and envelopes you in warmth –

**lighting that generates beauty** with every flip of the switch.

The logo consists of the letters 'LED' in a white, sans-serif font. The 'L' is a simple vertical bar. The 'E' is composed of three horizontal bars. The 'D' is a simple vertical bar with a curved top and bottom.

For more information on the quality and care TCP can deliver, call us at **800.324.1496** or visit [tcp.com](http://tcp.com)

325 Campus Dr. | Aurora, Ohio 44202 | P: 800-324-1496 | F: 330-995-6188