




GE
Lighting

90102 - GE LED PAR20

LED7DP202B830/20

 Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Rated Life (Hours)	25000 h
Bulb Shape	PAR20

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	3600 cd
Lumens per Watt (Efficacy)	73 lm
Nominal Initial Lumen per Watt	73
Rated Beam Spread	20 rad
Initial Lumens-nominal	520 lm
Color Rendering Index-CRI	83
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	90102
Description	LED7DP202B830/20
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168901024
Standard Package GTIN	00043168901024
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168901024
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS


Voltage <Nom>	120 V
Rated power (Watts)	7 W



GE
Lighting

90102 - GE LED PAR20

LED7DP202B830/20

 Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Rated Life (Hours)	25000 h
Bulb Shape	PAR20

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	3600 cd
Lumens per Watt (Efficacy)	73 lm
Nominal Initial Lumen per Watt	73
Rated Beam Spread	20 rad
Initial Lumens-nominal	520 lm
Color Rendering Index-CRI	83
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	90102
Description	LED7DP202B830/20
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168901024
Standard Package GTIN	00043168901024
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168901024
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	7 W