



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED7T824G8CSJDX2 7W Led T8 24" 3K/35K/4K/5K/65K SGL/DBL End - Glass *Keystone Technologies*

Catalog Number	LED7T824G8CSJDX2
Manufacturer	Keystone Technologies
Description	7W Led T8 Tube, 1000 Lumen, Glass Construction, 2FT, Color Select 3000/3500/4000/5000/6500K, 120-277V Input, Direct Drive, Single and Double Ended Wiring
Weight per unit	0.0160 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1000
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	7
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	N/A
housing color	N/A

Descriptions

Construction	Frosted Shatterproof Glass
Description	7W LED T8 24" 3K/35K/4K/5K/65K SGL/DBL END - GLASS
extra long description	Key KT-LED7T8-24G-8CSJ-DX2 7W LED T
Long Description	7W LED T8 Tube, 1000 lumen, Glass Construction, 2ft, Color Select 3000/3500/4000/5000/6500k, 120-277v Input, Direct Drive, Single and Double Ended Wiring
Product Type	7W Led T8 Tube, 1000 Lumen, Glass Construction, 2FT, Color S



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654141428
Manufacturers Part Number	KT-LED7T8-24G-8CSJ-DX2
UPC	843654141428

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	------------------------------------------------------------------

Packaging

Carton	25
Weight Per each	0.016

Uses, Certifications, and Standards

Energy Star	N
-------------	---