



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED8.5A19F82710Y 8.5W Led A19 27K 800LM ND *Sylvania-Ledvance*

Catalog Number	LED8.5A19F82710Y
Manufacturer	Sylvania-Ledvance
Description	Led A19, 8.5W 80CRI, 800 Lumen, 2700K, 11000 Life, E26 Mediumbase, Frosted Finish
Weight per unit	0.2050 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

Base	E26 Medium
Lamp Type	LED A19
lumens	800
Shape	A19
Voltage	120.00 V
Voltage Rating	120.00
Wattage	8.50

Material, Color, and Finish

color rendering index (cri)	80
Style	A-shape

Dimensions and Weight

Size	2.36
------	------

Descriptions

Description	8.5W LED A19 27K 800LM ND
extra long description	SYL LED8.5A19F82710YVRP/73885 LED8.
Long Description	LED A19, 8.5W 80CRI, 800 Lumen, 2700K, 11000 Life, E26 MediumBase,FROSTED Finish

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135738852
Manufacturers Part Number	LED8.5A19F82710YVRP/73885
UPC	046135738852

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
----------------------	------------------------

Packaging

Carton	1
Package	6
Weight Per each	0.205

Uses, Certifications, and Standards

standard	cETLus
----------	--------