

SHOE BOX/WALL PACK RETROFITS

80W LED-8089M

Replaces up to 250W

Ask about our metal halide ballast compatible models




Includes support feet to prevent socket sag



120W LED-8090M*

Replaces up to 400W

Type V, IV, III Optics



DESCRIPTION			LUMENS	POWER USED	REPLACES	BASE	CCT			DIMENSIONS
LED-8087E 30W SHOE BOX / WALL PACK <i>Type V Optics</i>	LED-8087E40-A	LED-8087E40-A (120V) LED-8087E40C-A (347V)	Up to 4171	30W	100W	E26 Edison	4000K	✓		6" x 2.75"
	LED-8087E57-A	LED-8087E57-A (120V) LED-8087E57C-A (347V)	Up to 4225	30W	100W	E26 Edison	5700K	✓		6" x 2.75"
LED-8087M 30W SHOE BOX / WALL PACK <i>Type V Optics</i>	LED-8087M40-A	LED-8087M40-A (120V) LED-8087M40C-A (347V)	Up to 4000	30W	100W	E39 Mogul	4000K	✓		6.7" x 2.75"
	LED-8087M57-A	LED-8087M57-A (120V) LED-8087M57C-A (347V)	Up to 4000	30W	100W	E39 Mogul	5700K	✓		6.7" x 2.75"
LED-8088E 50W SHOE BOX / WALL PACK <i>Type V Optics</i>	LED-8088E40	LED-8088E40C	Up to 5946	50W	175W	E26 Edison	4000K	✓		7.87" x 3.75"
	LED-8088E57	LED-8088E57C	Up to 5826	50W	175W	E26 Edison	5700K	✓		7.87" x 3.75"
LED-8088M 50W SHOE BOX / WALL PACK <i>Type V Optics</i>	LED-8088M40	LED-8088M40C	Up to 5946	50W	175W	E39 Mogul	4000K	✓	✓	8.47" x 3.75"
	LED-8088M57	LED-8088M57C	Up to 5826	50W	175W	E39 Mogul	5700K	✓	✓	8.47" x 3.75"
LED-8089M 80W SHOE BOX / WALL PACK <i>Type V Optics</i>	LED-8089M40	LED-8089M40C	6910	80W	250W	E39 Mogul	4000K	✓	✓	11.4" x 4.3"
	LED-8089M50	LED-8089M50C	7403	80W	250W	E39 Mogul	5000K	✓	✓	11.4" x 4.3"
LED-8090M 120W SHOE BOX / WALL PACK <i>Type V Optics</i>	LED-8090M40-A	LED-8090M40-A (120V) LED-8090M40C-A (347V)	Up to 12293	120W	400W	E39 Mogul	4000K	✓	✓	11.4" x 4.3"
	LED-8090M50-A	LED-8090M50-A (120V) LED-8090M50C-A (347V)	Up to 12590	120W	400W	E39 Mogul	5000K	✓	✓	11.4" x 4.3"
LED-8090M 120W SHOE BOX / WALL PACK <i>Type IV Optics</i>	LED-8090M4T4	LED-8090M4C4	8483	120W	400W	E39 Mogul	4000K	✓	✓	11.4" x 4.3"
	LED-8090M5T4	LED-8090M5C4	10165	120W	400W	E39 Mogul	5000K	✓	✓	11.4" x 4.3"
LED-8090M 120W SHOE BOX / WALL PACK <i>Type III Optics</i>	LED-8090M4T3	LED-8090M4C3	9584	120W	400W	E39 Mogul	4000K	✓	✓	11.4" x 4.3"
	LED-8090M5T3	LED-8090M5C3	10566	120W	400W	E39 Mogul	5000K	✓	✓	11.4" x 4.3"

* Utility Patent Pending 14/710,301

VOLTAGE: 120-277VAC 120-347VAC • >80 CRI • 50,000 HOUR RATED LIFE • 5 YEAR WARRANTY