



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED8088M50G4 50W Led WLPK LMP 50K Mog Base *Light Efficient Design*

Catalog Number	LED8088M50G4
Manufacturer	Light Efficient Design
Description	50W Shoe Box/Wall Pack Retrofit , Replaces Up to 175W Hid, EX39, 5000K EX39 Replaces Up to 175W Hid 120-277V
Weight per unit	1.3 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Base	EX39
beam angle	Type V
dimnable	No
lumens	7250
Power Factor	175W HID
Voltage Rating	120-277
Wattage	50

Material, Color, and Finish

color rendering index (cri)	>80
color temperature	5000

Dimensions and Weight

Diameter	3.75
Length	8.5

Descriptions

Description	50W LED WLPK LMP 50K MOG BASE
extra long description	LED LED-8088M50-G4 50W SHBX/WLPK RT
Long Description	50W SHOE BOX/WALL PACK RETROFIT , REPLACES UP TO 175W HID, EX39, 5000K EX39 REPLACES UP TO 175W HID 120-277V
Product Type	50W SHBX/WLPK RTFT REP175W HIDEX39 5000K

Manufacturer Information

Brand	Light Efficient Design
GTIN	00844006083472
Manufacturers Part Number	LED-8088M50-G4
UPC	844006083472

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
----------------------	-------------------------------

Packaging

Carton	1
Weight Per each	1.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

cULus
