



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED8T8L24FG850G7 8W Led T8 24" 50K 1250LM Glass

Sylvania-Ledvance

Catalog Number	LED8T8L24FG850G7
Manufacturer	Sylvania-Ledvance
Description	OBS75523 2FT Substitube Led T8, Frosted Glass, 8W, 82CRI, 1250 Lumens, 5000K, 50, 000 Life
Weight per unit	0.3670 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	G13
Lamp Type	LED T8
Shape	T8
Wattage	8.00

Material, Color, and Finish

color rendering index (cri)	82
Style	Tube, double-ended

Dimensions and Weight

Size	1.02
------	------

Descriptions

Description	8W LED T8 24" 50K 1250LM GLASS
extra long description	SYL LED8T8L24FG850SUBG7/75523 LED8T
Long Description	OBS75523 2ft SubstiTUBE LED T8, frosted glass, 8W, 82CRI, 1250 Lumens, 5000K, 50,000 life
Product Type	LED8T8L24FG850SUBG7 10/CS 1/Sku

Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135755231
Manufacturers Part Number	LED8T8L24FG850SUBG7/75523
UPC	046135755231

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Package	10
Weight Per each	0.367

Uses, Certifications, and Standards

standard	UL
----------	----