



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED9.5A190840G2 9.5W Led A19 40K Dim 800LM 80cri *Keystone Technologies*

Catalog Number	LED9.5A190840G2
Manufacturer	Keystone Technologies
Description	A19 Omni-Directional Bulb, 60W Equivalent, E26 Medium Base, 4000K, 80 Cri
Weight per unit	0.1220 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	230 Deg
Circuit Type	N/A
Input Voltage	120V
ip rating	N/A
lumens	800
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	3
Wattage	9.5
Wire Type	N/A

Material, Color, and Finish

Base Type	E26
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	N/A
Description	9.5W LED A19 40K DIM 800LM 80CRI
extra long description	Key KT-LED9.5A19-O-840 /G2 60W Equi
Long Description	A19 Omni-Directional Bulb, 60W Equivalent, E26 Medium Base, 4000K, 80 CRI
Product Type	60W Equiv., 9.5W, 800 Lumen, A19, E26, =80 Cri, Dimmable 27K



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654130200
Manufacturers Part Number	KT-LED9.5A19-O-840 /G2
UPC	843654130200

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
----------------------	------------------------

Packaging

Carton	1
Package	60
Weight Per each	0.122

Uses, Certifications, and Standards

Energy Star	Y
-------------	---