



Product Number: 78035

Order Abbreviation: LED9A19DIMO827URP

General Description: LED A19, 9W, Dimmable, 80CRI, 800 Lumen, 2700K, 15000 life

Product Information

| | |
|------------------------------|------------------------------|
| Life Time (L70) | 15000 |
| Operating Temperature (°C) | -20 to 45 |
| Dimming | Yes |
| Abbrev. With Packaging Info. | LED9A19DIMO827URP 6/CS 1/SKU |
| Average Rated Life (hr) | 15000 |
| Base | E26 Medium |
| Bulb | A19 |
| Family Brand Name | ULTRA |
| Color Temperature/CCT (K) | 2700 |
| Color Rendering Index (CRI) | 80 |
| Lumens | 800 |
| Approx. Lumens | 800 |
| Nominal Voltage (V) | 120.00 |
| Nominal Wattage (W) | 9.00 |
| Language Strategy | ENGLISH/FRENCH |
| Ordering Abbreviation | LED9A19DIMO827URP |
| UPC Code | UPC046135780356 |
| Lamp Finish | Frosted |



Product Number: 78035

Order Abbreviation: LED9A19DIMO827URP

General Description: LED A19, 9W, Dimmable, 80CRI, 800 Lumen, 2700K, 15000 life

Product Information

| | |
|------------------------------|------------------------------|
| Life Time (L70) | 15000 |
| Operating Temperature (°C) | -20 to 45 |
| Dimming | Yes |
| Abbrev. With Packaging Info. | LED9A19DIMO827URP 6/CS 1/SKU |
| Average Rated Life (hr) | 15000 |
| Base | E26 Medium |
| Bulb | A19 |
| Family Brand Name | ULTRA |
| Color Temperature/CCT (K) | 2700 |
| Color Rendering Index (CRI) | 80 |
| Lumens | 800 |
| Approx. Lumens | 800 |
| Nominal Voltage (V) | 120.00 |
| Nominal Wattage (W) | 9.00 |
| Language Strategy | ENGLISH/FRENCH |
| Ordering Abbreviation | LED9A19DIMO827URP |
| UPC Code | UPC046135780356 |
| Lamp Finish | Frosted |