



LED-DK6-19W830-DIM



Description DISC LED GEN4 Downlight Kit 6 inch 19W - 1,200lm
Dimmable 2BD 80+CRI 120VAC E26 with GU24 Adapter

Ordering Code 08660

Specifications

Voltage Rating	120
Voltage Type	AC/DC
Watts	19
Base Type	Medium Screw (E26)
MOL in/mm	3.84/97.5
MOD in/mm	7.28/185
Lumens	1200
CT deg K	3000
CRI	80
Beam Angle	120
Rated Life	35,000
Ambient Operating Temp Range	-20° C (-4° F) to 40° C (104° F)

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



LED-DK6-19W830-DIM



Description DISC LED GEN4 Downlight Kit 6 inch 19W - 1,200lm
Dimmable 2BD 80+CRI 120VAC E26 with GU24 Adapter

Ordering Code 08660

Specifications

Voltage Rating	120
Voltage Type	AC/DC
Watts	19
Base Type	Medium Screw (E26)
MOL in/mm	3.84/97.5
MOD in/mm	7.28/185
Lumens	1200
CT deg K	3000
CRI	80
Beam Angle	120
Rated Life	35,000
Ambient Operating Temp Range	-20° C (-4° F) to 40° C (104° F)

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335